



Main

Product or component type	Blank plate
Number of gangs	1 gang
Colour tint	Metal gold hairline

Complementary

Material	Polycarbonate: plastic part
Device mounting	Surface Flush
Embedding depth	3.7 mm
Width	86 mm
Height	86 mm
Depth	13.4 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	52.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	676.0 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations