



### Main

Product or component type	Blank plate
Number of gangs	1 gang
Colour tint	Wood

### Complementary

Material	Polycarbonate: plastic part
Device mounting	Surface Flush
Width	86 mm
Height	86 mm
Depth	13.4 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	48.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	636.0 g

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations