



Main

Product or component type	Blank plate
Number of gangs	1 gang
Colour tint	Wine gold

Complementary

Material	Polycarbonate: plastic part
Device mounting	Surface Flush
Width	86 mm
Height	86 mm
Depth	13.4 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	52.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	72
Package 2 Height	21.0 cm
Package 2 Width	30.0 cm
Package 2 Length	39.5 cm
Package 2 Weight	4.558 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
