



### Main

Product brand	Schneider Electric
Range	AvatarOn
Product or component type	Connected dimmer

### Complementary

Concentrator compatibility	Wiser hub generation 1
Mobile App name	Wiser by SE
Device application	Light control
Device presentation	Complete product
Number of gangs	1 gang
Load type	Lamp: 300 W Fluorescent lamp: Halogen lamp: Incandescent lamp: LED lamp:
[Ue] rated operational voltage	100...240 V AC 50/60 Hz
Colour tint	White
Local signalling	Indicator: LED (white/blue) Programming indication: LED (green/red/orange)
Connections - terminals	Brass terminal, 1...2.5 mm <sup>2</sup> (AWG 18...AWG 13) solid Brass terminal, 1 x 2.5 mm <sup>2</sup>
Communication network type	Wireless Zigbee (2.4 GHz), 2.5 mW at < 50 m
Connections - terminals	Brass terminal
Embedding depth	35 mm
Depth	38.4 mm
Width	86 mm
Height	86 mm
Standards	IEC 60669-2-5 IEC 60669-1
Product certifications	Zigbee 3.0

### Environment

Environmental characteristic	Indoor use
Ambient air temperature for operation	-10...45 °C
IP degree of protection	IP20
Operating altitude	<= 2000 m
Quality labels	CE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	9.5 cm
Package 1 Length	5 cm
Package 1 Weight	133 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.42 kg
Unit Type of Package 3	P06
Number of Units in Package 3	480
Package 3 Height	105 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	115.96 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>