



Main

Range	AvatarOn
Product or component type	Card switch
Device application	Hotel
Load type	Resistive
Colour tint	Wine gold

Complementary

Device presentation	Complete product
Rated current	16 A at 250 V AC 50 Hz
Connections - terminals	Brass terminal
Clamping connection capacity	3 x 4 mm ² for solid cable(s) 3 x 4 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s) 2 x 2.5 mm ² for stranded cable(s)
Status LED	LED (amber)
Material	Polycarbonate: plastic part
Device mounting	Flush Surface
Width	86 mm
Height	86 mm
Depth	43.8 mm
Embedding depth	34.1 mm

Environment

IP degree of protection	IP20
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	0...60 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	0...95 %
Standards	IEC 60669-2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	124.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	9.0 cm
Package 2 Width	19.0 cm

Package 2 Length	19.5 cm
Package 2 Weight	1.042 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information