



Main

| | |
|---------------------------|---|
| Product or component type | Switch |
| Device application | Control |
| Load type | Incandescent lamp Inductive Resistive Fluorescent lamp |
| Colour tint | White |

Complementary

| | |
|------------------------------|--|
| Device presentation | Complete product |
| Rated current | 16 AX at 250 V AC 50/60 Hz |
| Switch function | 1-pole 2-way |
| Number of gangs | 1 gang |
| Number of rocker | 1 |
| Clamping connection capacity | 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s) |
| Connections - terminals | Brass terminal |
| Local signalling | Off: LED indicator, LED (amber) |
| Material | Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator |
| Device mounting | Flush Surface |
| Width | 86 mm |
| Height | 86 mm |
| Depth | 34.2 mm |

Environment

| | |
|---|--|
| IP degree of protection | IP20 |
| Maximum ambient air temperature for operation | 45 °C |
| Operating altitude | 2000 m |
| Relative humidity | 0...95 % |
| Standards | MS IEC 60669-1 IEC 60669-1 BS EN 60669-1 SS 227-1 |
| Environmental characteristic | UV resistant |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.4 cm |
| Package 1 Width | 8.6 cm |
| Package 1 Length | 8.6 cm |
| Package 1 Weight | 81.0 g |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 19.0 cm |
| Package 2 Length | 19.5 cm |
| Package 2 Weight | 887.0 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant with Exemptions |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |