



### Main

Product or component type	Telephone socket
Device application	Communication
Socket additional information	Shuttered
Number of gangs	1 gang
Material	PC (polycarbonate): housing Polycarbonate: plastic part
Colour tint	Dark grey
Colour tint	Dark grey

### Complementary

Device presentation	Complete product
Device mounting	Flush Surface
Communication network category	Voice: 3
Rated current	1.5 A
Contacts material	Contact: phosphor bronze with gold plating IDC contact: phosphor bronze with nickel plating
Contact resistance	1 $\mu$ Ohm
Insulation resistance	$\geq$ 200 MOhm
Minimum return loss	23 dB
Width	86 mm
Height	86 mm
Depth	40.7 mm

### Environment

Dielectric strength	1000 V for 60 s at 60 Hz
AWG gauge	AWG 26...AWG 22 (4 twisted pair cables)
Environmental characteristic	UV resistant
Maximum ambient air temperature for operation	45 °C
Relative humidity	0...95 %
Standards	TIA/EIA-568-B.2-1 ASTMD4566-98
IP degree of protection	IP20

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	62.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations