



Main

Product or component type	Telephone socket
Device application	Communication
Socket additional information	Shuttered
Number of gangs	1 gang
Material	PC (polycarbonate): housing Polycarbonate: plastic part
Colour tint	Metal gold hairline
Colour tint	Metal gold hairline

Complementary

Device presentation	Complete product
Device mounting	Surface Flush
Communication network category	Voice: 3
Rated current	1.5 A
Contacts material	Contact: phosphor bronze with gold plating IDC contact: phosphor bronze with nickel plating
Contact resistance	1 μ Ohm
Insulation resistance	\geq 200 MOhm
Minimum return loss	23 dB
Width	86 mm
Height	86 mm
Depth	40.7 mm

Environment

Dielectric strength	1000 V for 60 s at 60 Hz
AWG gauge	AWG 26...AWG 22 (4 twisted pair cables)
Environmental characteristic	UV resistant
Maximum ambient air temperature for operation	45 °C
Relative humidity	0...95 %
Standards	ASTMD4566-98 TIA/EIA-568-B.2-1
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	62.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10

Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	670.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations