



### Main

Product or component type	Cover plate
Accessory / separate part category	Mounting accessory
Colour tint	Metal gold hairline painted
Type of packing	Flow-pack
Main colour tint	Metal gold hairline

### Complementary

Colour tint	Metal gold hairline
Range compatibility	AvatarOn switch
Product destination	Switch
Number of rocker	1
Material	PC (polycarbonate)
Surface finish	Glossy
Surface treatment	Untreated
Device mounting	Flush
Height	86 mm
Width	86 mm
Depth	21 mm
Embedding depth	11.3 mm
Net weight	35 kg

### Environment

Ambient air temperature for storage	-5...45 °C
Ambient air temperature for operation	-5...45 °C
Product certifications	CCC
Standards	GB 17466

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.1 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	39.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	439.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations