



Main

Product or component type	Cover plate
Accessory / separate part category	Mounting accessory
Colour tint	Wood painted
Type of packing	Flow-pack
Main colour tint	Wood

Complementary

Colour tint	Wood
Range compatibility	AvatarOn switch
Product destination	Switch
Number of rocker	1
Material	PC (polycarbonate)
Surface finish	Glossy
Surface treatment	Untreated
Height	86 mm
Width	86 mm
Depth	21 mm

Environment

Ambient air temperature for storage	-5...45 °C
Ambient air temperature for operation	0...95 °C
Standards	BS 5733 IEC 60670

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.1 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	35 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	461 g
Unit Type of Package 3	CAR
Number of Units in Package 3	72
Package 3 Height	21 cm
Package 3 Width	30 cm

Package 3 Length	39.5 cm
Package 3 Weight	2.764 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations