



Main

Product or component type	Data socket
Device application	Communication
Socket additional information	Shuttered
Communication network category	Data: 6e
Number of gangs	2 gangs
Colour tint	Dark grey
Main colour tint	Dark grey

Complementary

Device presentation	Complete product
Device mounting	Surface Flush
Data socket type	RJ45
Rated current	1.5 A
Material	Polycarbonate: plastic part
Contacts material	Housing: PC Contact: phosphor bronze with gold plating
Contact resistance	1 μ Ohm
Insulation resistance	\geq 200 MOhm
Minimum return loss	23 dB
Colour tint	Dark grey
IP degree of protection	IP20
Width	86 mm
Height	86 mm
Depth	31 mm

Environment

Dielectric strength	1000 V for 60 s at 60 Hz
AWG gauge	AWG 26...AWG 22 (4 twisted pair cables)
Environmental characteristic	UV resistant
Maximum ambient air temperature for operation	35 °C
Relative humidity	0...95 %
Standards	ASTMD4566-98 TIA/EIA-568-B.2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	66.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations