



### Main

Product or component type	USB charger
Integrated connection type	2 USB type A 5 V DC, maximum load current: 2.1 A

### Complementary

Device mounting	Flush
Device presentation	Complete product
Colour tint	Dark grey
Surface finish	Glossy
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Maximum load current with 2 outputs used simultaneously	2.1 A
Material	PC (polycarbonate)
Connections - terminals	Screw terminals
Screwdriver shape	Phillips combined
Clamping connection capacity	1.5...2.5 mm <sup>2</sup> for flexible cable(s) 1.5...2.5 mm <sup>2</sup> for rigid cable(s)
Height	86 mm
Width	86 mm
Depth	40 mm

### Environment

Standards	IEC 60950-1
Electrical insulation class	Class II
IP degree of protection	IP20

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	104 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	882 g
Unit Type of Package 3	CAR

Number of Units in Package 3	48
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm
Package 3 Weight	4.992 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>