



Main

Product or component type	USB charger
Integrated connection type	2 USB type A 5 V DC, maximum load current: 2.1 A

Complementary

Device mounting	Flush
Device presentation	Complete product
Colour tint	Metal gold hairline
Surface finish	Glossy
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Maximum load current with 2 outputs used simultaneously	2.1 A
Material	PC (polycarbonate)
Connections - terminals	Screw terminals
Screwdriver shape	Phillips combined
Clamping connection capacity	1.5...2.5 mm ² for flexible cable(s) 1.5...2.5 mm ² for rigid cable(s)
Height	86 mm
Width	86 mm
Depth	40 mm

Environment

Standards	IEC 60950-1
Electrical insulation class	Class II
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	104.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm

Package 2 Length	19.5 cm
Package 2 Weight	882.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile
Minimum percentage of recycled plastic content	30