



Main

| | |
|---------------------------|---|
| Product or component type | Switch |
| Device application | Control |
| Load type | Inductive Incandescent lamp Resistive Fluorescent lamp |
| Colour tint | Wood |

Complementary

| | |
|------------------------------|--|
| Device presentation | Complete product |
| Rated current | 16 AX at 250 V AC 50/60 Hz |
| Switch function | 1-pole 2-way |
| Number of gangs | 4 gangs |
| Number of rocker | 4 |
| Clamping connection capacity | 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s) |
| Connections - terminals | Brass terminal |
| Local signalling | Off: LED indicator, LED (amber) |
| Material | Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator |
| Device mounting | Flush Surface |
| Width | 86 mm |
| Height | 86 mm |
| Depth | 34.2 mm |

Environment

| | |
|---|--|
| IP degree of protection | IP20 |
| Maximum ambient air temperature for operation | 45 °C |
| Operating altitude | 2000 m |
| Relative humidity | 0...95 % |
| Environmental characteristic | UV resistant |
| Standards | BS EN 60669-1 SS 227-1 MS IEC 60669-1 IEC 60669-1 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.4 cm |
| Package 1 Width | 8.6 cm |
| Package 1 Length | 8.6 cm |
| Package 1 Weight | 142 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 8 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 19 cm |
| Package 2 Length | 19.5 cm |
| Package 2 Weight | 1.248 kg |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 48 |
| Package 3 Height | 21 cm |
| Package 3 Width | 30 cm |
| Package 3 Length | 39.5 cm |
| Package 3 Weight | 7.487 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |