



Main

Product or component type	Switched socket
Device application	Power supply
Device presentation	Complete product
Outlet poles configuration	3P with shutter
Colour tint	Metal gold hairline
Type of packing	Flow-pack
Main colour tint	Metal gold hairline

Complementary

Rated current	13 A socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Socket number	2
Outlet standard description	With earthing contact
Outlet standard	British BS 1363A
Number of gangs	2 gangs
Service life in cycles	20000 cycles
Electrical durability	5000 cycles
Connections - terminals	Screw terminal
Material	Polycarbonate: grid plate Polycarbonate: surround
Surface finish	Glossy
Surface treatment	Painted mechanism cover
Device mounting	Surface
Fixing mode	Screw
Height	86 mm
Width	146 mm
Depth	31.7 mm

Environment

IP degree of protection	IP20
Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Standards	MS 589 SS 145 BS 1363
Product certifications	SIRIM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm

Package 1 Weight	151 g
Unit Type of Package 2	BB1
Number of Units in Package 2	7
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.107 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	42
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm
Package 3 Weight	7.142 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations