



Main

Range	AvatarOn
Product or component type	Shaver socket
Installation direction	Vertical
Input voltage	240 V AC 50/60 Hz
Output voltage	115 V AC 50/60 Hz 240 V AC 50/60 Hz
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: bracket Brass: terminals
Colour tint	Wood

Complementary

Device presentation	Complete product
Device mounting	Surface
Cable cross section	1...2.5 mm ²
Rated operational power in VA	20 VA
Connections - terminals	Pillar terminals
Width	86 mm
Height	147 mm
Depth	50 mm

Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	2000 m
IP degree of protection	IP21
Standards	IEC 61558-2-5

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	9.4 cm
Package 1 Length	15.3 cm
Package 1 Weight	150.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
