



## Main

Range	AvatarOn
Product or component type	Shaver socket
Installation direction	Vertical
Input voltage	240 V AC 50/60 Hz
Output voltage	115 V AC 50/60 Hz 240 V AC 50/60 Hz
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: bracket Brass: terminals
Colour tint	Wine gold

## Complementary

Device presentation	Complete product
Device mounting	Surface
Cable cross section	1...2.5 mm <sup>2</sup>
Rated operational power in VA	20 VA
Connections - terminals	Pillar terminals
Width	86 mm
Height	147 mm
Depth	50 mm

## Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	2000 m
IP degree of protection	IP21
Standards	IEC 61558-2-5

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	9.4 cm
Package 1 Length	15.3 cm
Package 1 Weight	154.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	16.3 cm
Package 2 Width	33.0 cm
Package 2 Length	50.4 cm
Package 2 Weight	3.3 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	41