



## Main

Range of product	AvatarOn C
Range	AvatarOn
Product or component type	Switched socket
Device application	Power supply
Device presentation	Basic element with complete housing
Outlet poles configuration	3P
Colour tint	Wine gold
Main colour tint	Wine gold

## Complementary

Rated current	15 A socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Socket number	1
Outlet standard description	3 pins
Outlet standard deviation	British
Number of gangs	1 gang
Material	PC (polycarbonate)
Device mounting	Surface
Fixing mode	By screws
Height	86 mm
Width	86 mm
Depth	35.3 mm

## Environment

IP degree of protection	IP20
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	82.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

---