



### Main

Range of product	AvatarOn C
Range	AvatarOn
Product or component type	Switched socket
Device application	Power supply
Device presentation	Basic element with complete housing
Colour tint	White
Main colour tint	White

### Complementary

Rated current	13 A socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Socket number	1
Outlet standard deviation	British
Number of gangs	1 gang
Material	PC (polycarbonate)
Device mounting	Surface
Fixing mode	By screws
Height	86 mm
Width	86 mm
Depth	30 mm

### Environment

IP degree of protection	IP20
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	75.9 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.3 cm
Package 2 Width	12.5 cm
Package 2 Length	26.5 cm
Package 2 Weight	0.86 kg
Unit Type of Package 3	S03
Number of Units in Package 3	90
Package 3 Height	30 cm
Package 3 Width	30 cm

Package 3 Length	40 cm
Package 3 Weight	9.14 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product