



Main

Range of product	AvatarOn C
Range	AvatarOn
Product or component type	Switched socket
Device application	Power supply
Device presentation	Basic element with complete housing
Colour tint	Wine gold
Main colour tint	Wine gold

Complementary

Rated current	13 A socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Socket number	1
Outlet standard deviation	British
Number of gangs	1 gang
Material	PC (polycarbonate)
Device mounting	Surface
Fixing mode	By screws
Height	86 mm
Width	86 mm
Depth	30 mm

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	75.9 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.3 cm
Package 2 Width	12.5 cm
Package 2 Length	26.5 cm
Package 2 Weight	0.86 kg
Unit Type of Package 3	S03
Number of Units in Package 3	90
Package 3 Height	30 cm
Package 3 Width	30 cm

Package 3 Length	40 cm
Package 3 Weight	9.14 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations