



### Main

Range of product	AvatarOn C
Product or component type	Bell press switch
Device application	Bell switch
Colour tint	Dark grey
Colour tint	Dark grey

### Complementary

Device presentation	Complete product
Rated current	10 A at 250 V AC 50/60 Hz
Switch function	Bell push switch
Switch application	Bell switch
Number of gangs	1 gang
Number of rocker	1
Connections - terminals	Screw terminal
Local signalling	With light indicator, fluorecent
Material	PC (polycarbonate)
Device mounting	Surface Flush
Width	86 mm
Height	86 mm
Depth	36.8 mm
Embedding depth	23.5 mm

### Environment

IP degree of protection	IP20
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	65.0 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product