

GS1AH02

Direct rotary handle, TeSys GS, black handle, right side mounting, 2 positions I-O, for GS 100 to 400A IEC



Main

Range of product	TeSys
Range	TeSys
Device short name	GS1AH
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS1 J TeSys TeSys GS GS1 K TeSys TeSys GS GS1 L TeSys TeSys GS GS1 N TeSys TeSys GS GS1P TeSys TeSys GS GS1Q
Type of operating handle	Direct right side
Handle colour	Black

Complementary

Handle positions	O-I
Rotary handle padlocking	With
Switch rated current	100 A 125 A 160 A 250 A 315 A 400 A
Standards	IEC
Net weight	0.1 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	3.000 cm
Package 1 Length	17.000 cm
Package 1 Weight	85.900 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.066 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------