



### Main

Range	TeSys
Product or component type	Enclosure
Device short name	GV2MP
Accessory / separate part category	Mounting accessory
Product compatibility	GV2ME
Enclosure type	Flush mounting

### Complementary

Auxiliary mounting location	Left Right
Height	140 mm
Width	106.5 mm
Depth	83 mm
Net weight	0.115 kg

### Environment

IP degree of protection	IP41 front face
Environmental characteristic	Standard environment

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	10 cm
Package 1 Length	15 cm
Package 1 Weight	219 g
Unit Type of Package 2	S04
Number of Units in Package 2	27
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	6.58 kg
Unit Type of Package 3	P06
Number of Units in Package 3	108
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	34.82 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------