

Main

Range	Lineryg
Product name	FT
Device short name	GV3G
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys Deca TeSys K TeSys U TeSys GV3
Product compatibility	LC1D40A...D65A GV3L GV3P
Number of tap-offs	3
[I _{th}] conventional free air thermal current	115 A
Connection pitch	64 mm




Complementary


Mounting location	On terminal
[U _i] rated insulation voltage	690 V
Net weight	0.25 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	5.0 cm
Package 1 Length	18.5 cm
Package 1 Weight	265.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	17
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.701 kg

Offer Sustainability

RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Contractual warranty	
Warranty	18 months

Set of Busbars GV3G364

