

Main

Range	TeSys
Product or component type	Clip-on connector
Device short name	GV7AC
Range compatibility	TeSys TeSys GV5 motor circuit breaker TeSys TeSys GV7 motor circuit breaker
Accessory / separate part category	Connection accessory

Complementary

[I _e] rated operational current	150 A
Connections - terminals	Screw terminal 1.5...95 mm ²
Quantity per set	Set of 3
Net weight	0.3 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	9.000 cm
Package 1 Length	10.000 cm
Package 1 Weight	173.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	24
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	4.918 kg
Unit Type of Package 3	P06
Number of Units in Package 3	48
Package 3 Height	50.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	18.336 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
SCIP Number	66ab381c-81b1-42a8-ae7a-ce3f5adb691a
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------
