



Main

| | |
|---------------------------|--------------------------|
| Range | TeSys TeSys Deca |
| Product or component type | Safety undervoltage trip |
| Device short name | GVAX |

Complementary

| | |
|---------------------------------|--|
| Range compatibility | TeSys GV2ME TeSys Deca |
| [Uc] control circuit voltage | 110...115 V AC 60 Hz |
| Control circuit voltage limits | 0.85...1.1 Un |
| [Ui] rated insulation voltage | 690 V AC conforming to IEC 60947-1 600 V AC conforming to UL 60947-4-1 600 V AC conforming to CSA C22.2 No 60947-4-1 |
| Threshold tripping voltage | 0.7...0.35 Un |
| Inrush power in VA | 12 VA AC |
| Inrush power in W | 8 W |
| Hold-in power consumption in VA | 3.5 VA AC |
| Hold-in power consumption in W | 1.1 W |
| Operating time | 10...15 ms conforming to IEC 60947-1 |
| On-load factor | 100 % |
| Connections - terminals | Screw clamp terminals 1 cable(s) 1...2.5 mm ² solid Screw clamp terminals 2 cable(s) 1...2.5 mm ² solid Screw clamp terminals 1 cable(s) 0.75...2.5 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 0.75...2.5 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 0.75...1.5 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.75...1.5 mm ² flexible with cable end |
| Tightening torque | < 1.4 N.m on screw clamp terminals |
| Mechanical durability | 30000 cycles |
| Quantity per set | Set of 10 |
| Height | 89 mm |
| Width | 18 mm |
| Depth | 66 mm |
| Net weight | 0.105 kg |
| Colour | Dark grey |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 8.3 cm |
| Package 1 Width | 3.6 cm |
| Package 1 Length | 9.1 cm |
| Package 1 Weight | 129.0 g |

Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

GVAX ...

