



### Main

Range	TeSys TeSys Deca
Product or component type	Safety undervoltage trip
Device short name	GVAX

### Complementary

Range compatibility	TeSys GV2ME TeSys Deca
[Uc] control circuit voltage	220...240 V AC 50 Hz
Control circuit voltage limits	0.85...1.1 Un
[Ui] rated insulation voltage	690 V AC conforming to IEC 60947-1 600 V AC conforming to UL 60947-4-1 600 V AC conforming to CSA C22.2 No 60947-4-1
Threshold tripping voltage	0.7...0.35 Un
Inrush power in VA	12 VA AC
Inrush power in W	8 W
Hold-in power consumption in VA	3.5 VA AC
Hold-in power consumption in W	1.1 W
Operating time	10...15 ms conforming to IEC 60947-1
On-load factor	100 %
Connections - terminals	Screw clamp terminals 1 cable(s) 1...2.5 mm <sup>2</sup> solid Screw clamp terminals 2 cable(s) 1...2.5 mm <sup>2</sup> solid Screw clamp terminals 1 cable(s) 0.75...2.5 mm <sup>2</sup> flexible without cable end Screw clamp terminals 2 cable(s) 0.75...2.5 mm <sup>2</sup> flexible without cable end Screw clamp terminals 1 cable(s) 0.75...1.5 mm <sup>2</sup> flexible with cable end Screw clamp terminals 2 cable(s) 0.75...1.5 mm <sup>2</sup> flexible with cable end
Tightening torque	< 1.4 N.m on screw clamp terminals
Mechanical durability	30000 cycles
Quantity per set	Set of 10
Height	89 mm
Width	18 mm
Depth	66 mm
Net weight	0.105 kg
Colour	Dark grey

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.800 cm
Package 1 Width	8.500 cm
Package 1 Length	9.500 cm
Package 1 Weight	121.000 g
Unit Type of Package 2	S01

Number of Units in Package 2	16
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.130 kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------

---

---

GVAX ...

