

Main

Range	Vivace
Product or component type	Switched socket
Device short name	KB15
Device presentation	Complete product

Complementary

Pilot light	Red neon indicator
Outlet poles configuration	2P + E
Number of gangs	1 gang
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	15 A at 250 V AC, resistive
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	Earth L N
Tightening torque	0.4 N.m
Clamping connection capacity	2.5 mm ²
Width	87 mm
Height	87 mm

Environment

Standards	SS 145 MS 589 BS 1362-2
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.2 cm
Package 1 Length	8.6 cm
Package 1 Weight	118 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	10 cm
Package 2 Weight	1.253 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	12140 g

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------