



Main

Range	Vivace
Product or component type	Switched socket
Device short name	KB15
Device application	Power supply Control
Device presentation	Complete product
Switch application	On/off switching
Main colour tint	White
Colour tint	White

Complementary

Outlet poles configuration	2P + E
Number of gangs	1 gang
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	22.0 mm
Rated current	15 A at 250 V AC, resistive
Network frequency	50/60 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	L Earth N
Tightening torque	0.4 N.m
Clamping connection capacity	2.5 mm ²
Width	87 mm
Height	87 mm
Depth	35 mm

Environment

Standards	MS 589 SS 145 BS 1362-2
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Operating altitude	<= 2000 m
Environmental characteristic	Indoor use
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.2 cm
Package 1 Length	8.6 cm
Package 1 Weight	118 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.25 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	31.5 cm
Package 3 Width	50 cm
Package 3 Length	50 cm
Package 3 Weight	12054 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------