



## Main

Range	Vivace
Product or component type	Blank plate
Accessory / separate part category	Installation accessories
Device short name	KB30
Device application	Cover
Colour tint	White

## Complementary

Fixing mode	By 2 screws
Range compatibility	Vivace cover frame
Number of gangs	1 gang
Colour tint	White
Surface finish	Glossy
Material	Polycarbonate: grid plate Polycarbonate: surround
Surface treatment	Untreated
Projecting depth	8 mm
Device mounting	Flush
Width	86 mm
Height	86 mm
IP degree of protection	IP20

## Environment

Standards	BS 5733
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	0...95 %
Operating altitude	0...2000 m
Environmental characteristic	Indoor use

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	8.6 cm
Package 1 Length	25.3 cm
Package 1 Weight	57.767 g
Unit Type of Package 2	BB1
Number of Units in Package 2	15
Package 2 Height	15 cm
Package 2 Width	38 cm
Package 2 Length	15 cm

Package 2 Weight	1.032 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	150
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8915 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------