



Main

Range	Vivace
Product or component type	Bell press switch
Device short name	KB31
Device application	Control
Additional switch application	Do not disturb
Switch function	1-way

Complementary

Device presentation	Complete mechanism
Actuator	Push-button
Pilot light	Indicator
Number of gangs	1 gang
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	10 A at 250 V AC, inductive 10 A at 250 V AC, resistive
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	N L1 COM L2
Tightening torque	0.4 N.m
Clamping connection capacity	<= 1.5 mm ²
Width	86 mm
Height	86 mm

Environment

Standards	MS IEC 60669-1 SS 227 IEC 60669-1
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.2 cm
Package 1 Length	8.6 cm
Package 1 Weight	98.6 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	859 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8141 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile