



Main

Range	Vivace
Device short name	KB31
Product or component type	Data socket
Device application	Communication
Cover type	Shutter
Device presentation	Complete mechanism
Colour tint	White

Complementary

Connector type	M-110 keystone RJ45 connector
Communication network category	6
Number of gangs	1 gang
Tightening torque	0.4 N.m
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Width	86 mm
Height	86 mm
Projecting depth	8 mm
Embedding depth	35 mm
Data socket type	RJ45 Cat.6
Main colour tint	White

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	FCC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	5 cm
Package 1 Length	8.6 cm
Package 1 Weight	83.7 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	15 cm
Package 2 Width	19 cm

Package 2 Length	10 cm
Package 2 Weight	907 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	31.5 cm
Package 3 Width	50 cm
Package 3 Length	50 cm
Package 3 Weight	8620 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes