




Main

Range	Vivace
Product or component type	Switch
Device short name	KB31
Device application	Lighting
Switch function	1-way

Complementary

Device presentation	Complete mechanism
Actuator	Rocker
Number of gangs	1 gang
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	16 AX at 250 V AC, inductive 16 AX at 250 V AC, fluorescent
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	L1 COM L2
Tightening torque	0.4 N.m
Clamping connection capacity	2.5 mm ²
Width	87 mm
Height	87 mm

Environment

Standards	MS IEC 60669-1 IEC 60669-1 SS 227
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	64 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	534 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	5962 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------