



Main

Range	Vivace
Device short name	KB32
Product or component type	Data socket
Device application	Communication
Cover type	Shutter
Device presentation	Complete mechanism
Colour tint	White

Complementary

Connector type	M-110 keystone RJ45 connector
Communication network category	6
Number of gangs	2 gangs
Tightening torque	0.4 N.m
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Width	86 mm
Height	86 mm
Projecting depth	8 mm
Embedding depth	35 mm
Data socket type	RJ45 Cat.6
Main colour tint	White

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	FCC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	5 cm
Package 1 Length	8.6 cm
Package 1 Weight	100.4 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm

Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	873 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8280 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------