

Main

Range	Vivace
Product or component type	USB charger
Device application	Power supply
Type of USB power supply	USB type A + A
Colour tint	Wall: white
Fixing mode	Screw

Complementary

Socket number	2
Device mounting	Flush
Device presentation	Complete product
Range compatibility	Vivace
Colour tint	White
[Ue] rated operational voltage	100/240 V AC at 50/60 Hz
Surface finish	Glossy
Connections - terminals	Screw terminal
Surface treatment	Untreated
Number of terminals	2
Number of modules	1 module 54.8 x 51.5 x 38.7 mm
Nominal output power	21 W
Type of packing	Plastic bag
Quantity per set	1
Sale per indivisible quantity	1
Condition of use	Room temperature
Ambient air temperature for storage	-5...60 °C
Relative humidity	10...90 %
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Output voltage	5 V DC, 2.1 A
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.1 A
Maximum load current with 2 outputs used simultaneously	2.1 A
Material	PC (polycarbonate): surround PC (polycarbonate): grid plate PA (polyamide) 6: housing Silicone rubber: cover
Shape of screw head	Cross
Number of terminals	2 screw terminals
Clamping connection capacity	2.5 mm ² for stranded cable(s) 2.5 mm ² for flexible cable(s) 2.5 mm ² for rigid cable(s) 1.5 mm ² for stranded cable(s) 1.5 mm ² for flexible cable(s) 1.5 mm ² for rigid cable(s)
Wire stripping length	6 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Product compatibility	Major smart phone and tablet HTC Samsung HW Apple XiaoMi Power bank
Standards	IEC 62368-1:2018
Height	87 mm
Width	87 mm
Depth	39 mm
Embedding depth	29.3 mm
Net weight	0.1042 kg
Main colour tint	White

Environment

Product certifications	CCC[RETURN]IEC
IP degree of protection	IP20
Environmental characteristic	Liquid soap Alcohol

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.5 cm
Package 1 Length	8.6 cm
Package 1 Weight	110 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	940 g

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	No

Contractual warranty

Warranty	1 Year
----------	--------