



Main

Range	Vivace
Product or component type	Shaver socket
Device short name	KBT
Device application	Power supply
Device presentation	Complete mechanism
Colour tint	Wall: white

Complementary

Number of gangs	2 gangs
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	120.6 mm
Embedding depth	40 mm
Rated current	At 115/240 V AC
Input voltage	115 V AC
Output voltage	240 V AC
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	L N E
Tightening torque	0.4 N.m
Clamping connection capacity	2.5 mm ²
Width	146 mm
Height	86 mm
Depth	47 mm

Environment

Standards	IEC 61558-2-5
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	0...95 %
Operating altitude	0...2000 m
Environmental characteristic	Indoor use
IP degree of protection	IP21

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	4.9 cm
Package 1 Length	14.6 cm
Package 1 Weight	671.5 g
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	2 cm
Package 2 Weight	1.413 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	20
Package 3 Height	31.5 cm
Package 3 Width	50 cm
Package 3 Length	50 cm
Package 3 Weight	13680 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------