



Main

Range	Vivace
Product or component type	Cover frame
Accessory / separate part category	Fixing accessory
Device short name	KB_41
Device application	Installation
Provided equipment	6 pieces of mechanical links
Colour tint	Wall: white

Complementary

Product destination	Flush mounted box
Fixing mode	By 2 screws
Range compatibility	Vivace KB_41 cover frame
Number of gangs	4 gangs
Colour tint	White
Surface finish	Glossy
Material	Polycarbonate: surround Polycarbonate: grid plate
Surface treatment	Untreated
Projecting depth	8 mm
Device mounting	Flush
Width	344 mm
Height	86 mm
Depth	8 mm
IP degree of protection	IP20

Environment

Standards	BS 5733
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Operating altitude	0...2000 m
Environmental characteristic	Indoor use

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	0.8 cm
Package 1 Length	34.7 cm
Package 1 Weight	90.2 g
Unit Type of Package 2	BB1
Number of Units in Package 2	18
Package 2 Height	9.5 cm

Package 2 Width	15 cm
Package 2 Length	38 cm
Package 2 Weight	1.693 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	72
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	6742 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------