



### Main

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	3P LC1D09...D38 4P LC1DT20...DT40 4P LC1D098...D258 CAD32, CAD50

### Complementary

Mounting location	Side
Mounting mode	By clips
Suppressor technology	RC circuit
[Uc] control circuit voltage	110...250 V AC
Maximum peak voltage	3 Uc
Net weight	0.012 kg

### Environment

Standards	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 60947-5-1 UL 60947-5-1 GB/T 14048.5
Product certifications	UL[RETURN]CSA
IP degree of protection	IP2X conforming to IEC 60529
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.100 cm
Package 1 Width	10.000 cm
Package 1 Length	5.000 cm
Package 1 Weight	14.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	70
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.207 kg
Unit Type of Package 3	P06
Number of Units in Package 3	2240
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm

Package 3 Length	80.000 cm
Package 3 Weight	48.539 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------