

Complementary

Control circuit voltage limits	Operational: 0.85...1.1 U _c (at <50 °C) Drop-out: 0.1...0.75 U _c (at <50 °C)
Inrush power in W	2.2 W (at 20 °C)
Hold-in power consumption in W	2.2 W at 20 °C
Heat dissipation	2.2 W

Environment

IP degree of protection	IP2X conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50015
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-50...70 °C
Operating altitude	2000 m without derating
Height	56 mm
Width	27 mm
Depth	55.5 mm
Net weight	0.132 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	5.9 cm
Package 1 Length	6.7 cm
Package 1 Weight	122.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.174 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------