



Main

Range	TeSys
Device short name	LT6CT
Product or component type	Current transformer
Range compatibility	TeSys TeSys T motor controller

Complementary

Current transformer ratio	400/1
Accuracy class	Class 5P
Precision limit factor	15
[Ui] rated insulation voltage	690 V
Diameter	35 mm
Cable cross section	300 mm ²
Height	107 mm
Width	95 mm
Depth	25 mm
Net weight	0.55 kg

Environment

Standards	BS 7626 IEC 60185
Maximum ambient air temperature for operation	50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.100 cm
Package 1 Width	10.500 cm
Package 1 Length	12.500 cm
Package 1 Weight	426.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.922 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------