



## Main

Range	MasterPact
Product or component type	Voltage release
Device application	Control
Range compatibility	Masterpact (MasterPact MTZ1) circuit-breaker Masterpact (MasterPact MTZ2) circuit-breaker Masterpact (MasterPact MTZ3) circuit-breaker
Voltage release type	Closing coil Opening coil

## Complementary

Control type	Communicating
Signalling function	Coil powered Error Electrical push-button activated Ready to close or open
[Un] voltage power supply	24/30 V AC 50/60 Hz 24/30 V DC
Threshold tripping voltage	0.7...1.1 Un on opening 0.85...1.1 Un on closing
Holding power consumption	4.5 W
Circuit breaker mounting mode	Fixed/drawout
Maximum response time	60 ms on opening for MasterPact MTZ1 60 ms on opening for MasterPact MTZ2 60 ms on opening for MasterPact MTZ3 65 ms on closing for MasterPact MTZ1 80 ms on closing for MasterPact MTZ2 90 ms on closing for MasterPact MTZ3
Provided equipment	1 instruction sheet
Offer type	Spare part

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.0 cm
Package 1 Length	8.5 cm
Package 1 Weight	235.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	16
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	4.373 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>