



Main

Range	MasterPact
Product or component type	Voltage release
Device application	Control
Range compatibility	Masterpact (MasterPact MTZ1) circuit-breaker Masterpact (MasterPact MTZ2) circuit-breaker Masterpact (MasterPact MTZ3) circuit-breaker
Voltage release type	Closing coil Opening coil

Complementary

Control type	Communicating
Signalling function	Ready to close or open Coil powered Error Electrical push-button activated
[Un] voltage power supply	277 V AC 50/60 Hz
Threshold tripping voltage	0.7...1.1 Un on opening 0.85...1.1 Un on closing
Holding power consumption	4.5 VA
Circuit breaker mounting mode	Fixed/drawout
Maximum response time	60 ms on opening for MasterPact MTZ1 60 ms on opening for MasterPact MTZ2 60 ms on opening for MasterPact MTZ3 65 ms on closing for MasterPact MTZ1 80 ms on closing for MasterPact MTZ2 90 ms on closing for MasterPact MTZ3
Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6 cm
Package 1 Length	8.4 cm
Package 1 Weight	155 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.085 kg
Unit Type of Package 3	S03
Number of Units in Package 3	10
Package 3 Height	30 cm

Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.085 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information