



## Main

Range	MasterPact
Device short name	CE/CD/CT
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact (MasterPact MTZ1) circuit breaker Masterpact (MasterPact MTZ2) circuit breaker Masterpact (MasterPact MTZ3) circuit breaker
Signal contacts composition	1 NO/NC

## Complementary

Auxiliary contacts type	Low level
Auxiliary contacts operation	Test position Disconnected position Connected position
Mounting mode	Drawout
[Ie] rated operational current	DC-12: 0.3 A at 250 V DC DC-12: 0.8 A at 125 V DC DC-12: 2.5 A at 24/48 V DC AC-12: 5 A at 24/48 V AC 50/60 Hz AC-12: 5 A at 240 V AC 50/60 Hz AC-12: 5 A at 380 V AC 50/60 Hz
Minimum load	2 mA at 15 V
Provided equipment	1 instruction sheet
Offer type	Spare part

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	5.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	63.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.594 kg

## Offer Sustainability

RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

---

China RoHS Regulation

 [China RoHS Declaration](#)

---

RoHS exemption information

 [Yes](#)

---