



Main

Range	MasterPact
Device short name	MCH
Product or component type	Motor mechanism
Device application	Control
Range compatibility	Masterpact MasterPact MTZ1

Complementary

Control type	Standard
[Uc] control circuit voltage	100...130 V AC 50/60 Hz
Threshold tripping voltage	0.85...1.1 Un
Maximum power consumption in VA	180 VA
Overcurrent protection	2...3 x In 0.1 s
Maximum charging time	3 s
Maximum operating frequency	<= 3 cycles per minute
Provided contact	Limit switch contact at 240 V 10 A

Environment

Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	14.0 cm
Package 1 Length	18.0 cm
Package 1 Weight	785.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information