



Main

Range	MasterPact
Product or component type	Voltage release
Device application	Control
Range compatibility	Masterpact MasterPact MTZ2 circuit-breaker Masterpact MasterPact MTZ3 circuit-breaker Masterpact MasterPact MTZ1 circuit-breaker
Voltage release type	Closing coil Opening coil

Complementary

[Un] voltage power supply	24 V AC 50 Hz 24...30 V DC
Threshold tripping voltage	0.7...1.1 Un on opening 0.85...1.1 Un on closing
Holding power consumption	4.5 W
Circuit breaker mounting mode	Fixed/drawout
Maximum response time	60 ms on opening for MasterPact MTZ1 60 ms on opening for MasterPact MTZ2 60 ms on opening for MasterPact MTZ3 65 ms on closing for MasterPact MTZ1 80 ms on closing for MasterPact MTZ2 90 ms on closing for MasterPact MTZ3
Provided equipment	1 instruction sheet
Offer type	Spare part

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.400 cm
Package 1 Width	14.200 cm
Package 1 Length	21.000 cm
Package 1 Weight	198.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	40
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	8.570 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information