

## Main

Maximum response time	45 ms on opening for MasterPact MTZ1 95 ms on opening for MasterPact MTZ2 95 ms on opening for MasterPact MTZ3
Range	MasterPact
Device short name	MN
Product or component type	Undervoltage release
Device application	Safety
Range compatibility	Masterpact MasterPact MTZ1 circuit breaker Masterpact MasterPact MTZ2 circuit breaker Masterpact MasterPact MTZ3 circuit breaker
Voltage release type	Instantaneous

## Complementary

Control type	Standard
[Un] voltage power supply	48 V AC 50/60 Hz 48...60 V DC
Threshold tripping voltage	0.35...0.7 Un opening 0.85 Un closing
Holding power consumption	4.5 W
Circuit breaker mounting mode	Fixed/drawout
Provided equipment	1 instruction sheet
Offer type	Spare part

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.0 cm
Package 1 Length	8.5 cm
Package 1 Weight	224.0 g

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
SCIP Number	Fb7b4f31-e2d2-4b8c-a9f0-9a1e2c43da19
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	174