



Main

Range	MasterPact
Device short name	MN delay unit
Product or component type	Time delay auxiliary
Device application	Control
Range compatibility	Masterpact MasterPact MTZ1 circuit breaker Masterpact MasterPact MTZ2 circuit breaker Masterpact MasterPact MTZ3 circuit breaker
Voltage release type	Instantaneous

Complementary

Impulse duration	200 ms
Time delay range	0.5...3 s
[Uc] control circuit voltage	380...480 V AC 50/60 Hz 380...480 V DC
Threshold tripping voltage	0.35...0.7 Un open 0.85 Un close
Supply holding power	4.5 VA
Supply inrush power	200 VA
Response time	0.5 s 0.9 s 1.5 s 3 s
Offer type	Spare part
Provided equipment	1 instruction sheet

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	8.5 cm
Package 1 Length	9.1 cm
Package 1 Weight	176.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.3 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes