



Main

Range	MasterPact
Device short name	CE
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact (MasterPact MTZ1) circuit breaker Masterpact (MasterPact MTZ2) circuit breaker Masterpact (MasterPact MTZ3) circuit breaker
Signal contacts composition	1 NO/NC

Complementary

Auxiliary contacts type	Standard
Auxiliary contacts operation	Connected position
Mounting mode	Drawout
[I _e] rated operational current	AC-12: 6 A at 690 V AC 50/60 Hz AC-12: 8 A at 240 V AC 50/60 Hz AC-12: 8 A at 380 V AC 50/60 Hz AC-12: 8 A at 480 V AC 50/60 Hz DC-12: 0.8 A at 125 V DC DC-12: 2.5 A at 24/48 V DC DC-12: 0.3 A at 150 V DC
Minimum load	100 mA at 24 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	4.2 cm
Package 1 Length	4.2 cm
Package 1 Weight	1.018 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.