



### Main

Maximum response time	95 ms on opening for MasterPact MTZ2 95 ms on opening for MasterPact MTZ3
Range	MasterPact
Device short name	MN diag
Product or component type	Undervoltage release
Device application	Safety
Range compatibility	Masterpact (MasterPact MTZ2) circuit breaker Masterpact (MasterPact MTZ3) circuit breaker
Voltage release type	Instantaneous

### Complementary

Control type	Communicating
Signalling function	Error Coil powered MN open
[Un] voltage power supply	380...480 V AC 50/60 Hz
Threshold tripping voltage	0.35...0.7 Un opening 0.85 Un closing
Holding power consumption	4.5 VA
Circuit breaker mounting mode	Drawout

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	6.0 cm
Package 1 Length	8.2 cm
Package 1 Weight	172.0 g

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>