



Main

Maximum response time	45 ms on opening for MasterPact MTZ1
Range	MasterPact
Device short name	MN diag
Product or component type	Undervoltage release
Device application	Safety
Range compatibility	Masterpact MasterPact MTZ1 circuit breaker
Voltage release type	Instantaneous

Complementary

Control type	Communicating
Signalling function	Error MN open Coil powered
[Un] voltage power supply	100...130 V AC 50/60 Hz 100...130 V DC
Threshold tripping voltage	0.35...0.7 Un opening 0.85 Un closing
Holding power consumption	4.5 W
Circuit breaker mounting mode	Drawout

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.0 cm
Package 1 Length	8.2 cm
Package 1 Weight	172.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.